



Synergy Global Technology Inc

www.RackmountMart.com


Metered Rack PDU

Outlets. The PDU has twenty-four (24) C13 outlets, four (4) C19 outlets, and two (2) L6-30 outlets.

Digital display. A digital display shows aggregate current being used per bank.

Power cord. The 3.04-m (10-ft) power cord terminates with a CS8365C connector.

ADH-030-CN-50A-CS-A



Specifications

Electrical

Input connector	CS8365C
Cord length	3.04 m (10 ft)
Nominal input voltage	200–240 V, 3-phase
Input frequency	50/60 Hz
Acceptable input voltage	+6%, –10% of nominal voltage
Maximum input current total (phase)	40 A
Nominal output voltage	200–240 V
Maximum output current Outlet Bank	15 A/C13; 16 A/C19; 24 A/L6-30 16 A/24 A
Output connectors	(24) C13, (4) C19, (2) L6-30
Overload protection Internal External (user-supplied)	(2) 20-A, (1) 30-A 2-pole breakers (1) 50-A 3-pole breaker

Physical

Dimensions (H × W × D) <i>(Including breaker box)</i>	1778 × 56 × 45 mm (70.00 × 2.20 × 1.75 in) 1778 × 56 × 95 mm (70.00 × 2.20 × 3.75in [†])
Shipping dimensions (H × W × D)	2057 × 311 × 79 mm (81 × 12.25 × 3.125 in)
Weight	10.36 kg (22.8 lb)

Environmental

Elevation (above MSL) Operating Storage	3000 m (10,000 ft) 15 000 m (50,000 ft)
Temperature Operating Storage	–5 to 45° C (23 to 113° F) –25 to 65° C (–13 to 149° F)
Humidity Operating/Storage	5–95%, non-condensing

Approvals

Safety Certification	UL/C-UL Listed, PSE
Emissions	FCC part 15 Class A, ICES-003 Class A, VCCI-A

[†] The depth with the breaker box (95 mm/3.75 in) extends for only a part (273 mm/10.75 in) of the height of the unit.

