

Universal open frame mounting




Display Benefits

- ▶ 19" widescreen LCD with high brightness 1000 cd/m<sup>2</sup>
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact

Options

- HDMI, DVI-D, S-Video + BNC & Audio
- 3G / HD / SD-SDI Broadcast-grade input
- MCS Multi-display control solution
- HW19" Touchscreen : Capacitive, Resistive, Multi-touch
- MIL-type or lockable connector
- 48V or 24VDC power
- TV - PAL or NTSC
- Auto / switch dimming



Standard I/O : VGA only

Options I/O : BNC + S-Video, Audio, TV, USB for touchscreen  
HDMI or DVI-D ( either one )

Specifications

LCD Panel

- Size (diagonal) : 19" TFT
- Max resolution : 1440 x 900
- Brightness (cd/m<sup>2</sup>) : 300
- Backlight : LED
- Colors : 16.7 M
- Contrast ratio (typ) : 1000 : 1
- Viewing angle (H/V) : 160° x 160°
- Active area (mm) : 408 x 255
- MTBF (hrs) : 50,000
- Signal input : VGA

Weight

- Net : 5 kgs ( 11 lbs )

Mounting :

Universal mount / VESA mount

Environmental

- Operating : 0 to 50°C Degree
- Storage : -5 to 60°C Degree
- Relative humidity : 5~90%, non-condensing
- Shock : 10G acceleration ( 11 ms duration )
- Vibration : 5~500Hz 1G RMS random vibration

Casing Color :

Dark grey ( RAL 7037 )

Regulatory :

FCC, CE

Power


- Input : Auto-sensing 100 to 240VAC, 50 / 60Hz
- Consumption : Max. 84 Watt, Standby 5 Watt

Dimensions


Product : 506 x 60 x 335 mm / 19.9 x 2.3 x 13.2 inch

Diagrams ( mm )

Front View



Side View



Rear View

