



## Specification

Smallest and lightest case with biggest size screen

### Dimension

15.9" (W) x 10.4" (H) x 7.8" (D)

40.4CM (W) x 26.4CM (H) x 19.8CM (D)

Full system weight: 30.0lbs (13.64 KGs)

### System Configuration

Black ABS fireproof chassis

15.1" TFT Color LCD: 1024 x 768

SBC Backplane: 7 PCI Slots (6 full size PCI + 1 half size PCI)

512MB DDRAM

40GB/80GB HDD (Optional)

1.44MB FDD

105 keys heavy-duty mechanical keyboard with built in touch pad (PS/2 Port) Optional track ball available.

Various available keyboard layouts in different languages

Slim CD-ROM (CD-RW, DVD Combo-Optional)

Built-in dual speakers

### Power Supply

Industrial level 300W power supply

Input voltage: 110/230 VDC @ 47/63Hz

Output voltage: +3.3V @ 28A, +5V @ 30A, +12V @ 22A, -5V @ 0.5A, -12V @ 0.8A+5VSB @ 2A UL/CSA/TUV/CE approved

### Cooling

Dual 8cm system fan

### Accessories

Carrying bag (Optional Trolley case with wheels), assembly parts, power cord

### Operating Temperature and relative humidity

0 to 50 degree C (32-133 degree F)

Relative Humidity from 5-85%

### OEM Specification Welcome