



32A model :	Fuse	MCB
VP30C13/6C19-32A-Wi/F_EN/2B-2	6	-
VP30C13/6C19-32A-Wi/CR_EN/2B-2	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details :
  - PH-1 < Bank 1 >** Output 16A max. C 13 # 1-9 (odd) + C 19 # C 1
  - < Bank 2 >** Output 16A max. C 13 # 2-10 (even) + C 19 # C 2
  - PH-2 < Bank 3 >** Output 16A max. C 13 # 1-9 (odd) + C 19 # C 1
  - < Bank 4 >** Output 16A max. C 13 # 2-10 (even) + C 19 # C 2
  - PH-3 < Bank 5 >** Output 16A max. C 13 # 1-9 (odd) + C 19 # C 1
  - < Bank 6 >** Output 16A max. C 13 # 2-10 (even) + C 19 # C 2

### Three phase monitored PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 x 30  
16A Rated IEC320 C19 x 6

### Meter Features ( Wi Monitored PDU + Outlet Measurement )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Current ( A ), Energy ( kWh ), Voltage ( V ) & Power factor  
 Outlet Measurement : Current ( A ), Energy ( kWh )  
 Accuracy : ±1% true RMS  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Dimension : 85 (W) x 90 (D) x 1700 (H) mm  
 Material : Steel  
 Color : White ( outlet bracket )  
 Black ( chassis )