


3-Phase 400V 32A individual fused monitored PDU : C13 x 18 + C19 x 6



32A model :	Fuse	MCB
VP18C13/6C19-32A-W/GF/CR_EN/2B-1	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 13 # 1 - 3 + C 19 # C 1
 < **Bank 2** > Output 16A max. C 13 # 4 - 6 + C 19 # C 2
PH-2 < **Bank 3** > Output 16A max. C 13 # 1 - 3 + C 19 # C 1
 < **Bank 4** > Output 16A max. C 13 # 4 - 6 + C 19 # C 2
PH-3 < **Bank 5** > Output 16A max. C 13 # 1 - 3 + C 19 # C 1
 < **Bank 6** > Output 16A max. C 13 # 4 - 6 + C 19 # C 2

Three phase monitored PDU

Outlet : 10A Rated IEC320 C13 with 5A individual fuse x 18
 16A Rated IEC320 C19 with 5A individual fuse x 6

Meter Features (W monitored PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Accuracy : ±1% true RMS
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1900 (H) mm
 Material : Extrusion
 Color : Black