


## 3-Phase 400V 32A monitored PDU : C13 x 30 + C19 x 12



32A model :	Fuse	MCB
VP30C13/12C19-32A-W/F_EN/2B-2	6	-
VP30C13/12C19-32A-W/CR_EN/2B-2	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details :
  - PH-1 < Bank 1 >** Output 16A max. C 13 #1-9(odd) + C 19 #C1, C3
  - < Bank 2 >** Output 16A max. C 13 #2-10(even) + C 19 #C2, C4
  - PH-2 < Bank 3 >** Output 16A max. C 13 #1-9(odd) + C 19 #C1, C3
  - < Bank 4 >** Output 16A max. C 13 #2-10(even) + C 19 #C2, C4
  - PH-3 < Bank 5 >** Output 16A max. C 13 #1-9(odd) + C 19 #C1, C3
  - < Bank 6 >** Output 16A max. C 13 #2-10(even) + C 19 #C2, C4

### Three phase monitored PDU

Outlet : 10A Rated IEC320 C13 x 30  
16A Rated IEC320 C19 x 12

### Meter Features ( W monitored PDU )

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 78 (W) x 70 (D) x 1775 (H) mm
- Material : Steel
- Color : White ( outlet bracket )  
Black ( chassis )