



FC CE UK

REACH

TAA
COMPLIANT

Benefits

- ▶ 1U 18" LCD display drawer
- ▶ 1920 x 1200 **WUXGA** native resolution / 16.7M colors
- ▶ HDMI 1.4 + VGA video input (speakers excluded)
- ▶ Short depth design of 460mm
- ▶ One Man installation design
- ▶ Enhanced aesthetics with molded front panel and two point lock
- ▶ TAA Compliant

Options

- Dual stereo speakers for HDMI
- DVI-D + Audio + Speakers
- DP 1.0 + Speakers
- Composite + Audio IN + Speakers
- 3G / HD / SD-SDI Broadcast-grade input + Speakers
- DC power : 12V / 24V / 48V / 125V / 250V

Product Specifications

Video	
Video input	HDMI 1.4 + VGA

LED-backlit LCD Panel	
Panel size (diagonal)	18"
Native resolution	1920 x 1200
Brightness (cd/m ²)	300
Contrast ratio (typ.)	1000 : 1
Colors	16.7 M
Viewing angle (L/R/U/D)	89/89/89/89
Response time (ms)	9
Dot pitch (mm)	0.202
Display area (mm)	387.76H x 242.35V
Surface treatment	Anti-glare
Surface hardness	3H
MTBF (hrs)	50,000

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption	Screen on	Max. 23W
	Power saving mode	Max. 2W
	Power button off	Max. 1W

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	10~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

Video Option		
Digital	Display port	DP 1.0 / HDCP 1.3
	DVI-D	DVI-D single link
	HDMI	HDMI 2.0 / HDCP 2.2
Analog	Composite (BNC)	NTSC & PAL

Audio Option		
Speaker	Dual stereo	2W x 2

Physical		
Dimensions (W x D x H)	Product	442 x 460 x 44 mm 17.4 x 18.1 x 1.73 inch
	Weight	11 kg / 24.2 lb

* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Mounting Distance	
Display drawer	490 ~ 720 mm 19.3 ~ 28.3 inch

Diagrams (mm)

