

# LCD2U17-05/ 19-04 2U Rackmount LCD Keyboard Drawer



- Monitor, keyboard with trackball/touchpad choice plus storage area occupies 2U of vertical 19" rack space.
- Included adjustable mounting depth ball bearing slides lock in the fully extended position.
- Monitor powers off preserving back light life when tilted down for sliding into the rack.
- Retainer and lock options to keep unit contained in the rack when not in use.
- Housed in rugged steel construction with a durable powder coat finish.
- Reduced rack depth for mounting in confined spaces.

## DISPLAY SPECIFICATIONS

<b>Display Type:</b>	Active matrix TFT LCD	<b>Resolution:</b>	640 x 350 640 x 480 800 x 600 1024 x 768 1280 x 1024
<b>Colors:</b>	16.7 million colors	<b>Display Area:</b>	17" - 17" Diagonal 19" - 19" Diagonal
<b>Contrast Ratio:</b>	17": 1000:1 typ. 19": 800:1 typ.	<b>Horizontal Frequency:</b>	31 to 80 KHz
<b>Brightness:</b>	17": 280 cd/m <sup>2</sup> typ. 19": 270 cd/m <sup>2</sup> typ.	<b>Vertical Frequency:</b>	55 to 76 Hz.
<b>Viewing Angle:</b>	Horizontal: 178° Vertical: 178°		
<b>Response Time:</b>	18ms typ.		

## GENERAL SPECIFICATIONS

<b>Chassis Dimensions:</b>	17": 19.0" (W) x 3.50" (H) x 13.25" (D) 19": 19.0" (W) x 3.50" (H) x 14.90" (D)
<b>Weight:</b>	20 lbs
<b>Power (TFT Display):</b>	90 - 260 VAC, 50/60 Hz. 60 Watts maximum
<b>On-Screen Controls:</b>	Brightness, Contrast, Horizontal & Vertical Position, Auto Adjust, OSD H & V Position, Load and Save Values
<b>Plug &amp; Play:</b>	DDC1 and DDC2B
<b>Temperature:</b>	Operating: 0°C to 50°C Storage: -20°C to 60°C
<b>Humidity:</b>	Operating: 10 to 85% RH (max)
<b>Input Signal (VGA):</b>	R.G.B. analog video, TTL H & V sync.
<b>Input Connector:</b>	Display: 15-pin mini D-Shell
<b>Colors Available:</b>	Black Specifications subject to change without notice.

## KEYBOARD AND MOUSE SPECIFICATIONS

<b>Rollover:</b>	Alpha N-key rollover.
<b>Auto repeat:</b>	Yes.
<b>Self Diagnostics:</b>	At power on and system reset.
<b>Data Buffer:</b>	All codes buffered before sending.
<b>Operating voltage:</b>	+5 VDC +/- 5%.
<b>Operating current:</b>	200 mA.
<b>Trackball Size:</b>	16mm (optical sensor)
<b>Touchpad Size:</b>	2.1" X 1.25"
<b>Buttons:</b>	Left and Right, Scroll(touchpad)
<b>Interface:</b>	PS/2, USB (U) optional.
<b>Compatibility:</b>	DOS, Windows 3.X, Windows 95/98, Windows NT, Windows 2000,XP.

## MODEL NUMBER

LCD2U17-05/19-04-(X)-(X)-(X)

- KB w/ 2-bottom touchpad = a
- KB w/ 3-bottom trackball = b
- Cherry™ KB w/ touchpad = c
- KB w/ 2-bottom trackball = d
- KB w/ 3-bottom touchpad = e

- Blank = Standard Front Panel
- R = Front Panel + Retainer Screws
- L = Front Panel + Lock
- U = USB connection
- bk = Black color
- lg = Light Grey color

Note: Only c, d, e version can be used with KVM  
Note: Only d, e version has storage area

Contact us about other options and additional rack mount products.