



LCDR7U17-04/8U19-04 17", 19" High Brightness Rackmount LCD Display

New



Diagram
Unit : mm



Options



BNC + S-Video



Touch Screen



Quad Display



DC Power



NEMA 4



DVI-D



Audio

LCD Display Benefits

- ▶ LED technology
- ▶ 800 cd/m2 for 17", 19" LCD
- ▶ Low power consumption
- ▶ Long lifetime up to 70,000 hours
- ▶ Minimum EMI emissions
- ▶ Operation temperature at -20°C
- ▶ High shock & vibration resistance
- ▶ Mercury free
- ▶ Slim size

Optical Bonding Option



- 1mm thick optically clear adhesive for touchscreen or 4mm temper glass
- No air gap between the cover glass & LCD panel
- Increased LCD durability under vibration
- Eliminate residual and ghost images

Anti-Reflective Film Option



- 0.1mm thick optical interference coating film
- Designed to provide visual enhancement
- Cost effective vacuum laminated technology
- Greatly reduced specular & diffuse reflection
- Increased contrast for improved readability
- Easy clean surface

Ordering Information

17" LCD Series

19" LCD Series

Model	LCDR7U17-04	LCDR8U19-04
-------	-------------	-------------

Dimensions

Model	Product Dimension (W x D x H)	Net Weight
LCDR7U17-04	480 x 57 x 310.3 mm 18.9 x 2.2 x 12.2 inch	7 kg / 15 lbs
LCDR8U19-04	480 x 57 x 354.8 mm 18.9 x 2.2 x 14 inch	8 kg / 18 lbs