



FC CE RoHS REACH

Data center demands the high quality cabinet level illumination. The stylist designed LED light bar is ideal and cost efficient to achieve the simple requirement.

By the integrated IR sensor, the LED light bar provides the Auto ON / OFF mode :

- Light ON when opening door
- Light OFF when closing door

The magnetic base of the light bar provides an easy, fast and tool-less affix.

Low-profile design allows flexible positioning which is perfect for the limited cabinet space.

## Key Benefits

### Auto ON / OFF



- Auto ON / OFF by IR sensor allows user friendly illumination
- Light ON when the door opened
- Light OFF when the door closed

### Easy Setup




- Magnetic base design for tool-less affix
- Low-profile design allows flexible positioning
- Simple components allow D I Y installation

### High Visibility




- 250 Lumens light output
- Cool white light for clear and superb view
- Color Temperature : 2850 - 7100k




**Single LED Package**  
Part no. RLB-101

- ① LED light bar x 1
- ② Auto switch power adapter



**Dual LED Package**  
Part no. RLB-101-2

- ① LED light bar x 2
- ② Auto switch power adapter
- ③ Y-power cable



Model Comparison		RLB-101	RLB-101-2
<b>ON / OFF</b>	Auto by IR sensor Sensing Distance		✓ 4 cm
<b>Light Bar No.</b>		1	2
<b>Light</b>	Color Lumens ( typ. ) Angel Color Temperature LED Life Expectancy	Cool White 250 LM 120° Degree 2850 - 7100K 30,000 hrs	
<b>Power</b>	Input Consumption	Auto-sensing 100V or 240VAC via power adapter 4.5 Watt ( 12V ) per LED light bar	
<b>Housing</b>	Chassis Diffuser Affix	Extruded aluminum with silver powder coat Acrylic with milky white Magnetic base for unrestricted installation	
<b>Environmental</b>	Operating	-20 to 40°C Degree ( Indoor )	
<b>Dimensions</b>	Product ( L x W x H )	300 x 25 x 13.5 mm	
<b>Weight</b>	Net	86g ( per LED )	
<b>Regulatory</b>	Safety / Environmental	CE & FCC certified / RoHS & REACH compliant	

**1A Power Adapter Plug Selection**



BS1363



CEE 7/16



NEMA 1-15P  
(Default)



AS 3112

**2.5A Power Adapter ( optional )**

with 6 ft C13 - C14 power cord



IEC C14