



### Key Benefits

- ▶ 1920 x 1080 native Full HD resolution
- ▶ 16.7M colors
- ▶ High brightness panel 1000nits ( option )
- ▶ DVI-D / VGA video input
- ▶ HDMI / Display port video input ( option )
- ▶ Video decoding capability up to 1080p ( option )
- ▶ Rugged structure ensures high mobility
- ▶ Professional-use durability & around-the-clock operation

### Applications

- Broadcasting / Advertising
- Traffic control / Command center
- Directory / Ticket kiosk
- Surveillance system
- Vehicle mount display
- Bathroom TV

## Options

### Video Management & Transmission over Network

- HDMI Decoder Module 1080p over IP
- HDMI Receiver Module 1080p
- Multi Monitor OSD Control Module over serial
- 3G / HD / SD-SDI Input Module
- Auto / Manual Brightness Dimming Module (for High Bright model)

### Bezel & Frame Customization

- Dimension
- Color & Treatment
- Screen Printing
- Stainless Steel Bezel

### Touchscreen & Glass Protection

- Resistive 1-point Touch
- Projected Capacitive 10-point Touch
- Anti-reflective Glass
- Vandal Proof Glass

### DC Power & connector


- 12V / 24V / 48V / 110V / 125V / 250VDC
- MIL-type or lockable connector

### Mounting

- VESA mount kit
- Desktop stand
- Wall mount

## Diagrams ( mm )


Front View



Side View



Rear View



## Product Specifications

LCD Panel	ID-E19Dw	ID-HE19Dw
Panel size (diagonal)	18.5"	
Native resolution	1920 x 1080	
Brightness (cd/m <sup>2</sup> )	350	1000
Contrast ratio (typ.)	1000 : 1	1000 : 1
Colors	16.7 M	
Viewing angle (L/R/U/D)	89/89/89/89	
Response time (ms)	20	
Dot pitch (mm)	0.213	
Display area (mm)	408.96H x 230.04V	
Surface treatment	Anti-glare, Hard-coating	
Surface hardness	3H	
Backlight type	LED	
MTBF (hrs)	50,000	

Video	
VGA	Analog 0.7Vp-p
DVI	DVI-D single link

Video Option	
Display port	DP1.0 / HDCP 1.3
HDMI	HDMI 1.4 / HDCP 1.4
Composite (BNC)	NTSC & PAL

Audio ( option )	
Audio input :	
Connector	3.5mm stereo jack
Impedance / Power level	30kΩ / 750mV
Audio output :	
Connector	3.5mm stereo jack
Resistance / Power level	30kΩ / 2.8V
Speaker :	
Dual stereo speaker	2W x 2

\*When the audio output is connected, speaker output is OFF

Power	ID-E19Dw	ID-HE19Dw
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption :		
Screen on	Max. 12W	Max. 40W
Power saving mode	Max. 2W	Max. 2W
Power button on	Max. 1W	Max. 1W

Environment	
Operating temp.	-20 to 70°C degree
Storage temp.	-20 to 70°C degree
Operating humidity	5 to 95°C degree
Storage humidity	5 to 95°C degree
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration ( 11ms duration )
Vibration	10~300Hz 0.5G RMS random vibration

Design	ID-E19Dw / HE19Dw
Protection	Front Cover
Front panel	Black, RAL 9005
Rear casing	Black, RAL 9005

Mounting	ID-E19Dw / HE19Dw
VESA mount	100 x 100 mm
Universal mount	-
Desktop stand	option
Wall mount	option

Physical	ID-E19Dw / HE19Dw
Product (W x D x H) :	
mm	477.9 x 61.2 x 287.5
inch	18.8 x 2.4 x 11.3
Net weight	6.3 kg / 13.9 lb

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

DVI-D / VGA input	HDMI input	Display port input
<b>PC signal :</b> 1920 x 1080 x 60Hz 1360 x 768 x 60Hz 1280 x 1024 x 60 / 75Hz 1280 x 960 x 60Hz 1280 x 768 x 60 / 75Hz 1152 x 864 x 75Hz 1024 x 768 x 60 / 70 / 75Hz 848 x 480 x 60Hz 800 x 600 x 60 / 72 / 75Hz 720 x 400 x 70Hz 640 x 480 x 60 / 72 / 75Hz 640 x 400 x 70Hz 640 x 350 x 70Hz	<b>PC signal :</b> Same as VGA  <b>HDMI 1.3 / 1.4 :</b> 1920 x 1080 x 50 / 60Hz 1920 x 1080 x 25 / 30Hz 1280 x 720 x 50 / 60Hz 720 x 480 x 50 / 60Hz	<b>PC signal :</b> 1920 x 1080 x 60Hz 1600 x 1200 x 60Hz 1360 x 768 x 60Hz 1280 x 768 x 60 / 75Hz 1280 x 768 x 60Hz 1024 x 768 x 60 / 70 / 75Hz 800 x 600 x 60 / 72 / 75Hz 720 x 400 x 70Hz 640 x 480 x 60 / 72 / 75Hz
<b>Audio signal :</b> 2ch Linear PCM	<b>Audio signal :</b> 2ch Linear PCM	<b>Audio signal :</b> 2ch Linear PCM