


## CR1011 19" Server Rack Cabinet



### Feature:

- Easy assemble
- Good air ventilation
- Water or dust resist from top
- You could increase to total 8 fans
- All doors design with the spring latch, easy remove, tool less

### Dimension:

- Inside Dimension :
- Height = 24U ( 43" )    Width = 19"
- Depth = 32.25" (Self-tapping type) /32.75" (Square type,Optional)
- Overall Dimension : 23.50"(w) x 35.50"(d) x 52"(h)

### Package content :

- Die-cast heavy duty aluminum post frame
- Plexiglass front door W/lock
- Heavy duty sheet metal side and rear doors W/lock
- Top and bottom panels W/cable access hole
- Full size mounting strips front and rear
- 3 of 12cm fans (115CFM each) on top
- 4 heavy duty wheels
- 4 leveling feet
- 50 pcs M6 bolt screws W/washer
- Grounding wires

### Specification :

- Interior width: Hole to Hole = 19", Railing to Railing = 17 5/8"
- Depth of front railing to rear door: Self-tapping type = 32.25"    Square type = 32 11/16" ,Optional
- Maximum length of sliding rail's brackets: Self-tapping type = 27 11/16"    Square type = 29 9/16"

### Optional Accessories:

Air Filters  
Blank Panels  
Bracket Supports  
Cable Management  
KVM Switches  
Rack Cooling Fans  
Rack Display Mounting Brackets  
Rack Drawers  
Rack Keyboard Drawers (No Monitor & KVM)

Rack LCD Monitors (No Keyboard & KVM)  
Rack LCD Monitor Keyboard Optional KVM  
Rack PDU ( Power Distribution Unit )  
Rack Rails  
Rack Shelves  
Rack Speakers  
Power Strips  
Screw Bags  
Vertical Mounting Rail