


Steel Structures

Cooling Fans on Rear Door

Silence Enhance Foam



Cable Entry

Depth-Adjustable Rack System with Square Mounting Holes

Glass Front Door

Removable Side Panels with Quick Latches and Keylock

Keylock on Front/ Rear Doors

Heavy Duty Casters



Model No.	Form Factor	Dimension (inches)			Assembly Required?	Loading Capacity (lbs)	Door	Internal Depth	Removable Side panels	Security	Casters
		W	H	D							
QCR0901	9U	23.62	24.21	35.43	No	2200	Yes	Height: 17" Max Depth: 30"	Yes	Key Lock	Yes

9U 900mm Depth Ultimate Quiet Server Cabinet

Introduction

The QCR0901 is built with high-quality aluminum/steel structures with silence enhance foam inside the cabinet, which absorbs the noise from equipment and keeps it from going out. It is a cost-effective solution for people who need a peace working environment. Also, six 120mm cooling fans with low rpm on the rear door provide excellent air circulation for servers and other devices. Cabinets are completely lockable from the front/ rear doors and side panels to prevent unauthorized access.



Specifications

Color	Black
Material	Frame: Aluminum Base: SPCC Cold Rolled Steel t1.2 Mounting Rails: SPCC Cold Rolled Steel t2.0 Top Panel: SPCC Cold Rolled Steel t1.2 Side Panels: SPCC Cold Rolled Steel t1.2 Doors: SPCC Cold Rolled Steel t1.5
Cooling	6 x 120mm 120V AC fans
Basic Equipment	Lockable Side Panels w/ Quick Lockers Silence Enhance Foam
Internal Dimensions	Height: 17" Max Depth: 30"

Features

- Universal Fit Most of Rackmount Chassis and Equipment
- Front, Rear, and Side Security Lock to Prevent Unauthorized Access to Equipment and Data
- 6 x 120mm Cooling Fans on Rear Door
- Silence Enhance Foam to Absorb Noise from Equipment
- Cable Entry Provided from Bottom
- Fully Adjustable Rails to Ensure the Best Fit of Rack-mount Chassis

