


## 3-Phase 400V 32A individual fused monitored PDU : C19 x 18



32A model :	Fuse	MCB
VP18C19-32A-W/GF/CR_EN/2B-1	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A single pole hydraulic MCB x 6
- Bank Details :
  - PH-1 < Bank 1 >** Output 16A max. C 19 # C 1 - C 3
  - < Bank 2 >** Output 16A max. C 19 # C 4 - C 6
  - PH-2 < Bank 3 >** Output 16A max. C 19 # C 1 - C 3
  - < Bank 4 >** Output 16A max. C 19 # C 4 - C 6
  - PH-3 < Bank 5 >** Output 16A max. C 19 # C 1 - C 3
  - < Bank 6 >** Output 16A max. C 19 # C 4 - C 6

### Three phase monitored PDU

Outlet : 16A Rated IEC320 C19 with 5A individual fuse x 18

### Meter Features ( W monitored PDU )

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 70 (W) x 83 (D) x 1650 (H) mm
- Material : Extrusion
- Color : Black