


3-Phase 400V 16A monitored PDU + outlet measurement : C19 x 18



16A model :	Fuse	MCB
VP18C19-16A-Wi/F_EN/2B-2/LOCK	3	-
VP18C19-16A-Wi/CR_EN/2B-2/LOCK	-	3

- Input Rating : 16A, 400V
- Inlet : 16A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 3
- Phase Details : < PH-1 > Output 16A max. C 19 # C 1 - C 6
< PH-2 > Output 16A max. C 19 # C 1 - C 6
< PH-3 > Output 16A max. C 19 # C 1 - C 6

Three phase monitored PDU + outlet measurement

Outlet : 16A Rated IEC320 C19 (lockable) x 18



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2015 Synergy Global Technology Inc. All rights reserved.

Meter Features (Wi Monitored PDU + Outlet Measurement)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
- Outlet Measurement : Current (A), Energy (kWh)
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1325 (H) mm
- Material : Steel
- Color : White (outlet bracket)
Black (chassis)