


## 3-Phase 400V 32A monitored PDU : C13 x 18 + C19 x 6



32A model :	Fuse	MCB
VP18C13/6C19-32A-W/CR_EN/2B-1/LOCK	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A single pole hydraulic MCB x 6
- Bank Details :
  - PH-1 < Bank 1 >** Output 16A max. C 13 #1-3 + C 19 # C 1
  - < Bank 2 >** Output 16A max. C 13 #4-6 + C 19 # C 2
  - PH-2 < Bank 3 >** Output 16A max. C 13 #1-3 + C 19 # C 1
  - < Bank 4 >** Output 16A max. C 13 #1-3 + C 19 # C 1
  - PH-3 < Bank 5 >** Output 16A max. C 13 #1-3 + C 19 # C 1
  - < Bank 6 >** Output 16A max. C 13 #1-3 + C 19 # C 1

### Three phase monitored PDU

Outlet : 10A Rated IEC320 C13 (lockable) x 18  
16A Rated IEC320 C19 (lockable) x 6

### Meter Features ( W monitored PDU )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
Accuracy : ±1% true RMS  
IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
Cascade : Up to 16 PDU under single IP address via IP dongle  
SNMP : via IP dongle  
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified  
Safety Compliance : CE / LVD certified  
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
Storage Temperature : -25 to 65 °C  
Operating Altitude : 0 to 2,000 m  
Storage Altitude : 0 to 15,000 m  
Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1900 (H) mm  
Material : Extrusion  
Color : Black