


PDU specification drawing

3-Phase 400V 32A monitored PDU : C13 x 30



32A model :	Fuse	MCB
VP30C13-32A-W/F_EN/2B-2/LOCK	6	-
VP30C13-32A-W/CR_EN/2B-2/LOCK	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 6
- Bank Details :
 - PH-1 < Bank 1 >** Output 16A max. C 13 # 1 -9 (odd)
 - < Bank 2 >** Output 16A max. C 13 # 2 -10 (even)
 - PH-2 < Bank 3 >** Output 16A max. C 13 # 1 -9 (odd)
 - < Bank 4 >** Output 16A max. C 13 # 2 -10 (even)
 - PH-3 < Bank 5 >** Output 16A max. C 13 # 1 -9 (odd)
 - < Bank 6 >** Output 16A max. C 13 # 2 -10 (even)

Three phase monitored PDU

Outlet : 10A Rated IEC320 C13 (lockable) x 30

Meter Features (W monitored PDU)

- Local Display : Field replaceable 2.8" color LCD with touchscreen
- Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
- Accuracy : ±1% true RMS
- IP Access : via IP dongle, one IP Access up to 16 PDU Levels
- Cascade : Up to 16 PDU under single IP address via IP dongle
- SNMP : via IP dongle
- Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

- EMC Compliance : FCC & CE certified
- Safety Compliance : CE / LVD certified
- Environment Compliance : RoHS2 & REACH

- Operating Temperature : -5 to 60 °C
- Storage Temperature : -25 to 65 °C
- Operating Altitude : 0 to 2,000 m
- Storage Altitude : 0 to 15,000 m
- Humidity : 8 to 95% RH, non-condensing

- Dimension : 100 (W) x 90 (D) x 1700 (H) mm
- Material : Steel
- Color : White (outlet bracket)
Black (chassis)