

# LCDK5002 1U COMPACT KEYBOARD WITH COMPUTER

( MADE IN USA )

## New Product

**INTRODUCTORY PRICE**  
(4Gb DDR3 memory, 32Gb SSD Drive,  
operating system additional)

Model Numbers:  
LCDK5002-b032/LCDK5002-n032



### COMPUTER SPECIFICATIONS

- 1.86 GHz Dual Core Intel® N2800 Atom™ processor.
- Intel® NM10 Express chipset.
- Intel® Graphics Media Accelerator 3650 with:  
1 VGA port and 1 HDMI port.
- Six external USB 2.0 ports (2 high current).
- 2+2 channel Intel® High Definition Audio with multi-streaming.
- Intel® 82574L 10/100/1000 Mb/s Ethernet Controller.
- 4 GB DDR3 1066 memory standard.
- Internal PCI Express Mini Card connectors for SSD, etc.
- 110/220 VAC 50/60 Hz to 5A 12 VDC power supply included.



Computer Power Switch  
and activity indicators



Convenient access to  
computer I/O Panel

### KEYBOARD SPECIFICATIONS

- Keys:** 87 keys with Windows key
- Rollover:** Alpha N-key rollover.
- Auto repeat:** Yes.
- Self Diagnostics:** At power on and system reset.
- Pointing Device:** 14mm Optical Trackball or Touchpad.
- Reliability:** 5M switch life cycles



2 rear panel USB ports



External Optical and Hard Drive  
storage space




### GENERAL SPECIFICATIONS

- Dimensions:** 19.0" (W) x 1.75" (H) x 16.00" (D) (18.75 D w/Cable Management)
- Slides:** 14" (16" extension) Adjustable for 14" to 24" mounting depth.
- Weight:** 13 lbs
- Temperature:** Operating: 0°C to 50°C Storage: -20°C to 60°C
- Humidity:** Operating: 10 to 85% RH Non Condensing (max)

Prices and specifications subject to change without notice.

### MODEL NUMBER

LCDK5002-( kb type )-( SSD )-( front panel )



Additional options and configurations available.

