


Features

- Meet MIL-STD-810F/G standard
- 1U 19" rack mount LCD drawer, wide operation temperature support 1280 x 1024 resolution
- MIL connector for power input
- Standard with DVI-D, VGA, Audio input
- Front osd control buttons to optimized display
- Build in 2x 2watts stereo speakers

Options

- Composite video input
- HDMI or Display port input
- BNC input
- DC 9~36V power input
- High brightness LCD panel, up to 1000 nits
- Front AR or EMC glass protect screen
- Resistive touch screen



Rear of MIL1U19-011

Part No.		MIL1U19-011
LCD	Size	19"
	Backlight	LED
	Resolution	1280 x 1024
	Max.color	16.7M
	Luminance	450cd/m2
	View Angel (H/V)	170 / 160
	Contrast Ratio	1000 : 1
Touch Screen		Yes, for option
Input Signal	DVI-D	DVI-D 24Pin Connector (Female)
	VGA	D-SUB 15Pin Connector (Female)
	Audio	3.5" Jack
Rack Depth		600mm to 800mm (rack cabinet front rails to rear rails)
Power		100-240V AC 50/60Hz via 4 pins lock connector
Environment (MIL-STD-810G)	Operation temp: -20 to 70°C	(MIL-STD-810, Method 501.5 & 502.5)
	Storage temp: -30 to 80°C	(MIL-STD-810, Method 501.5 & 502.5)
	Humidity: 5% - 95%, non-condensing	(MIL-STD-810, Method 507.5)
	Shock/Vibration: Procedure VI, 50G @ 11ms	(MIL-STD-810, Method 516.6)
	Altitude: 10,000 ft Operational, 30,000 ft Storage	(MIL-STD-810, Method 500.5)
Physical Dimensions / Net Weights		448 x 44 x 600 mm (WxHxD) /17.5 KG